

IMPORTANT INFORMATION FOR TESTING AGM TYPE BATTERIES

CTEK BATTERY ANALYZER (EN)

The internal resistance of an AGM starter battery is lower than a comparable wet battery so the Analyzer will give a consistently higher reading.

To improve accuracy for a given AGM battery rating the Analyzer setting should be adjusted according to the 'correction factor' table **before** performing the test.

The test result can then be read as if the 'actual' value had been input in the first place.

AGM CORRECTION FACTOR TABLE

BATTERY AGM RATING EN	BATTERY ANALYZER SETTING
180	225
230	275
280	325
330	400
360	425
420	500
480	575
520	625
540	650
600	725
640	775
680	825
760	900
790	950
860	1025
900	1075
940	1125
1000	1200
1040	Out of range
1080	Out of range
1150	Out of range



THE SMARTEST BATTERY CHARGERS IN THE WORLD